

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 12/07mm**

**Order data**

Order number	269989 12/07
GTIN	4067263787143
Item class	21T

**Technical description**

Centre offset $L_3$	8 mm
Overall length L	140 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A12L SDQCR/L07
Shank Ø $D_s$	12 mm
Clamping height $L_2$	11 mm
Head length $L_1$	25 mm
Pack of insert screws	269028 7
Minimum pre-drill Ø $D_{min}$	15 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar