

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/11mm


Order data

Order number	269988 16/11
GTIN	4067263787105
Item class	21T

Technical description

Centre offset L_3	14 mm
ISO code toolholder	A16Q SDQCR/L11
Shank $\varnothing D_s$	16 mm
Head length L_1	28 mm
Clamping height L_2	15 mm
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{min}$	23 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 8
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar