



## COLOUR MATCH LED true colour rechargeable work lamp, Type: MULTI-R



### Order data

Order number	081514 MULTI-R
GTIN	5708997356586
Item class	08C

### Description

#### Version:

**COLOUR MATCH.** Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **MULTIMATCH R.** Powerful, portable battery work light with continuous CCT SCAN function. Rear display

Battery capacity and remaining runtime. Integral adjustment base for direct mounting on Scangrip stand 081252 1.35-3.

With stepless CCT SCAN function. When activated, the lamp automatically scans the surface of the object with the entire colour spectrum range. Locking is possible at any time. Ideal for detecting paint defects.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Charging cable.

### Technical description

CRI value	95
Illumination	120 - 1200 lm
Type of rechargeable battery	Lithium-ion
Overall length	165 mm
Number of rechargeable batteries contained	1
IP Index of Protection	IP 67
ATEX zone	None
Illumination time	1 - 10 h
Weight	820 g
Overall width	155 mm
Power supply	Mains operated
Type of product	Work lamp