

**Garant**
**GARANT Master eco clamp toolholder, left-hand, Shank / insert size: 25/12mm**

**Order data**

Order number	250039 25/12
GTIN	4067263122104
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Insert size	12 mm
ISO code toolholder	DCLNR/L 2525M12
Shim	259031 49
suitable indexable insert	CN.. 1204..
Functional width L <sub>4</sub>	32 mm
Head length L <sub>1</sub>	30 mm
Overall length L	150 mm
Shim screw	259027 8
Series	Master Eco
Shank size	25 mm
Clamp, screw, O-ring	259036 22

Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder

---

## Accessories

Shim Type 49	259031 49
Clamp unit Type 22	259036 22
Shim screw Type 8	259027 8