

Garant
**GARANT Master eco clamp toolholder, right-hand, Shank / insert size:
25/08mm**

Order data

Order number	251914 25/08
GTIN	4067263122340
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shank size	25 mm
Overall length L	150 mm
Series	Master Eco
Shim screw	259027 9
Head length L ₁	35 mm
Insert size	8 mm
Shim	259033 6
Functional width L ₄	32 mm
ISO code toolholder	DWLNR/L 2525M08
suitable indexable insert	WN.. 0804..

Clamp, screw, spring	259036 25
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder