

Garant
GARANT Master eco clamp toolholder, left-hand, Shank / insert size: 20/08mm

Order data

Order number	251915 20/08
GTIN	4067263122357
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shim	259033 6
Series	Master Eco
Head length L ₁	35 mm
Shim screw	259027 9
Shank size	20 mm
Insert size	8 mm
Clamp, screw, spring	259036 26
suitable indexable insert	WN.. 0804..
ISO code toolholder	DWLNR/L 2020K08
Functional width L ₄	25 mm
Overall length L	125 mm

Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder