

**Garant**
**GARANT Master eco screw-on toolholder, right-hand, Shank / insert size: 25/11mm**

**Order data**

Order number	260292 25/11
GTIN	4067263122494
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Shim screw	269013 7
Insert size	11 mm
Shank size	25 mm
Pack of insert screws	269023 3
Overall length L	150 mm
Shim	269007 1
suitable indexable insert	DC.. 11T3..
Series	Master Eco
ISO code toolholder	SDJCR/L 2525M11
Functional width L <sub>4</sub>	32 mm

Head length $L_1$	30 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder