

**Garant**
**GARANT Master eco screw-on toolholder, left-hand, Shank / insert size: 20/11mm**

**Order data**

Order number	260293 20/11
GTIN	4067263122517
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Overall length L	125 mm
Shim screw	269013 7
Shim	269007 1
Insert size	11 mm
Series	Master Eco
ISO code toolholder	SDJCR/L 2020K11
Head length L <sub>1</sub>	30 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269023 3
Functional width L <sub>4</sub>	25 mm

Shank size	20 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder