


Garant
GARANT Master eco screw-on toolholder short, left-hand, Shank / insert size: 16/11mm

Order data

Order number	261137 16/11
GTIN	4067263122630
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Overall length L	85 mm
Shank size	16 mm
Series	Master Eco
ISO code toolholder	SVJCR/L 1616X11
Functional width L ₄	20 mm
Head length L ₁	35 mm
suitable indexable insert	VC.. 1103..
Insert size	11 mm
Pack of insert screws	269023 1
Standard	Works standard

Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder