

Garant
KNUX 160405L, Grade: HB7130-2

Order data

Order number	251032 HB7130-2
GTIN	4067263342038
Item class	21G

Description

KNUX 160405L HB7130-2 Grade: HB7130-2

Chip breaker: VM

Chip diverter: 2.2 mm

Cutting depth a_p : 0.5 - 5 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 70 - 240 m/min

Technical description

Cutting speed v_c main application	70 - 240 m/min
Cutting depth a_p	0.5 - 5 mm
Coating	coated
Chip diverter	2.2 mm
Chip breaker	VM
Tool material	Carbide
Cutting conditions	continuous
Number of changes/inserts	2
Grade	HB7130-2
Finishing/roughing assignment	Finishing

Main application	M
Feed f	0.2 - 0.5 mm/rev.
Corner radius	1 mm
ISO code indexable insert	KNUX 160405L
Type of product	Indexable insert for turning