

Garant**CC.T 120408, Grade: HB7140-2**

Order data

Order number	260160 HB7140-2
GTIN	4067263315599
Item class	21G

Description

CC.T 120408 HB7140-2 Grade: HB7140-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.2 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 60 - 200 m/min

Technical description

Coating	coated
ISO code indexable insert	CCMT 120408
Corner radius	0.8 mm
Tolerance	M
Number of changes/inserts	2
Cutting speed v_c main application	60 - 200 m/min

Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 4 mm
Grade	HB7140-2
Cutting conditions	heavily interrupted
Tool material	Carbide
Main application	M
Chip breaker	VM
Type of product	Indexable insert for turning