

**“Hold fast” pot magnet, AlNiCo, Ø: 55mm****Order data**

Order number	085968 55
GTIN	2050000965333
Item class	08Q

Description**Version:**

To lift the magnet from the component via a press release spindle. With 2 tapped holes M8 for fixing brackets.

Technical description

Ø	55 mm
Number of attachment tapped holes	2
Weight	1 kg
Tapped attachment hole in the magnet head	M8 mm
Nominal clamping force	400 N
Magnet body height	49.2 mm
Material of the magnet core	AlNiCo
Type of product	Pot magnet

