

**Cordless drill / driver ProCORE, Type: GSR1890C****Order data**

Order number	070245 GSR1890C
GTIN	4059952617244
Item class	03B

Description**Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Kick-back control with automatic shut-down if jammed, together with unique precision clutch and motor brake. 13 mm auto-lock metal drill chuck. High torque.

Can be retrofitted with a **connectivity** module.

Supplied with:

Supplied with 2× Li-ion batteries, quick charger and L-BOXX.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Technical description

maximum torque hard	64 Nm
---------------------	-------

maximum twist drill size Ø in steel	13 mm
Motor design	Brushless motor
Weight	1.1 kg
maximum twist drill size Ø in wood	68 mm
maximum torque soft	36 Nm
Speed range 1st speed	0 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
Interface	Bluetooth interface
Packaging	Modular case (L-Boxx)
Battery capacity	4 Ah
Number of rechargeable batteries contained	2
maximum vibration to EN	<2,5 m/s ²
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
Manufacturer's designation	GSR 18V-90 C
Type of rechargeable battery	Lithium-ion
Speed range 2nd speed	0 - 2100 min ⁻¹
Type of product	Drill/driver
USP1	18V
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, in L-Boxx