



## Cordless drill / driver without battery, Type: GSR1890C



### Order data

Order number	070246 GSR1890C
GTIN	4059952617213
Item class	03B

### Description

#### Version:

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Can be retrofitted with a **connectivity** module.

#### Supplied with:

Including L-BOXX **without** battery and charger.

#### Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

### Technical description

Speed range 2nd speed	0 - 2100 min <sup>-1</sup>
maximum twist drill size Ø in steel	13 mm
Motor design	Brushless motor

Quick-clamping chuck range	1.5 - 13 mm
Number of rechargeable batteries contained	0
Packaging	Modular case (L-Boxx)
maximum torque hard	64 Nm
maximum twist drill size Ø in wood	68 mm
Power supply	Mains operated
maximum vibration to EN	<2,5 m/s <sup>2</sup>
typical application	Strong
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
Speed range 1st speed	0 min <sup>-1</sup>
Manufacturer's designation	GSR 18V-90 C
Weight	1.1 kg
maximum torque soft	36 Nm
Type of rechargeable battery	Lithium-ion
Type of product	Drill/driver
USP1	18V
USP2	Brushless motor, with softgrip, without battery, in L-Boxx