

**LED cordless lamp, 12 V, Type: GLI12300****Order data**

Order number	073203 GLI12300
GTIN	3165140876179
Item class	03B

Description**Version:**

12 V work light with 10 LEDs and two brightness levels. Adjustable angle up to 200°, suspension hook, carabiner and integral magnet.

Supplied with:

Cordless lamp without battery and without charger.

Note:

Suitable spare batteries and chargers can be found under No. 073851– 073866.

Technical description

Battery voltage	12 V
Weight including rechargeable battery	0.3 g
Number of rechargeable batteries contained	1
Illumination	300 lm
Type of rechargeable battery	Lithium-ion
Weight without battery	0.15 g

Manufacturer's designation	GLI 12V-300
Illumination time	3 h
Power supply	Mains operated
ATEX zone	None
Bulb	LED lamp
Product name attribute	12 V
suitable battery - supplier / battery type / voltage	Bosch 12 V
Type of product	Work lamp