

**Cordless angle grinders, Type: GWX18V10SC****Order data**

Order number	077010 GWX18V10SC
GTIN	
Item class	03C

**Description****Version:**

- **Easy and quick:** Easy change of angle grinder accessories without parts that could be lost or need for additional tools.
- **Additional wrench no longer required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** thanks to completely tool-less and quick accessory replacement.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Maximum user protection thanks to acoustic signal upon correct mounting.
- **Clean working without annoying scratches! Less prominent and fewer scuffs with X-Lock angle grinders.**

The angle grinder has a Bluetooth connectivity module and user interface, as well as drop control, X-brake and kickback control. It is possible to change accessories quickly and conveniently thanks to the keyless X-LOCK click system.

The Bluetooth connectivity module allows adjustments directly via the Toolbox app and a user interface with speed preselection ensures maximum comfort with active tool feedback.

**Supplied with:**

Supplied with 2 pcs. ProCORE18V 5.5Ah, quick charger GAL 1880 CV, additional vibration control handle, safety guard, L-BOXX.

**Technical description**

Packaging	Modular case (L-Boxx)
maximum disc Ø	125 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Manufacturer's designation	GWX 18V-10 SC
Toolholder	X-LOCK system
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Power supply	Mains operated
Number of rechargeable batteries contained	2
Motor design	Brushless motor
Weight including rechargeable battery	2.9 kg
Weight	2 kg
Weight without battery	2 kg
Speed range	4500 - 9000 min <sup>-1</sup>
Kick-back stop	yes
Special features	Variable speed; Kickback Control; Drop Control
Restart block	yes
Battery capacity	5.5 Ah
Type of product	Angle grinder