



Cordless angle grinder GWS, Type: GWS1810SC



Order data

Order number	077120 GWS1810SC
GTIN	4059952647524
Item class	03C

Description

Version:

Powerful **18 V cordless angle grinder**.

- **30 % more power and 125 % longer run time thanks to the new EC motor and the new ProCORE 18-V battery technology.**
- **Increased safety thanks to the intelligent brake system which shortens the brake time by up to 70 % and KickBack Control.**
- **User comfort thanks to keyless disc change.**

Supplied with:

Includes 2 pcs. ProCORE 18 V rechargeable battery, mounting flange, charger, quick clamping nut, 1 pc. Bluetooth Low Energy Module GCY 42 Professional, safety guard and L-BOXX.

Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers.

Technical description

Soft start	no
maximum cutting depth	34 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum vibration to EN	6 m/s ²
Battery capacity	5.5 Ah

Number of rechargeable batteries contained	2
maximum disc Ø	125 mm
Overload protection	yes
Weight	2 kg
Kick-back stop	yes
Restart block	yes
Power supply	Mains operated
maximum speed	4500 - 9000 min ⁻¹
Manufacturer's designation	GWS18V-10SC
Dead man's circuit	no
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Packaging	Modular case (L-Boxx)
Type of product	Angle grinder

Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type 1880CV	073866 1880CV