

**C-hook (pin) spanner with square pin, for external nut Ø: 65/70mm****Order data**

Order number	628400 65/70
GTIN	4020772054403
Item class	63Q

**Description****Version:**

Special steel, drive head ground, hardened and burnished.  
Hook spanner with square pin to DIN 1810 A.

**Application:**

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

**Note:**

Sizes 135/145; 260/270 thickness is different to DIN. Size not included in DIN, dimensions similar to DIN.

**Technical description**

Manufacturer's designation	DIN 1810A
for external nut Ø	65 - 70 mm
overall length	240 mm
Type	1810A
Type of product	C-hook (pin) spanners