

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 2000mm**Order data**

Order number	940803 2000
GTIN	4067263559900
Item class	9GI

Description**Version:**

Empty cabinet in 20×20G. Suitable drawers: 16×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	49 kg
Usable height	1845 mm
Type of cabinet	Base cabinet
Electronic locking system can be retrofitted	yes

Depth	500 mm
Handle positioning	centre
ComfortClose	no
Depth in G	20
Width in G	20
Width	500 mm
Height	2000 mm
Cabinet fronts	Plain sheet metal swing door
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves