

Garant GRIDLINE

## Base cabinet with plain sheet metal swing doors, Height: 2000mm



### Order data

Order number	940801 2000
GTIN	4067263559092
Item class	9GI

### Description

#### Version:

Empty cabinet in 20×20G. Suitable drawers: 16×16G (please order these separately)  
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Cabinet fronts	Viewing window swing door
Depth	500 mm
Weight	49 kg
Depth in G	20

Usable height	1845 mm
Width in G	20
ComfortClose	no
Type of cabinet	Base cabinet
Width	500 mm
Handle positioning	centre
Height	2000 mm
Electronic locking system can be retrofitted	yes
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves