

**PU braided hose, blue, Length 25 m, Hose internal Ø (nominal bore): 13mm****Order data**

Order number	080221 13
GTIN	7391390300461
Item class	08A

Description**Version:**

Very light, flexible, and abrasion-resistant PU hose. Outstanding resistance to oil, solvents, and non-aqueous solvents. Operating pressure 16 bar.

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.

Technical description

Hose external Ø	18 mm
Material	PU braided hose
Hose length	25 m
Hose internal Ø (nominal bore)	13 mm
Colour	blue
maximum operating pressure	16 bar
Product name attribute	Length 25 m
Type of product	Hose

