

Garant GREENPLUS

GARANT GreenPlus ultrasonic cleaner Sonic Cleaner AL-D, alkaline demulsifying, Contents: 5l



Order data

Order number	088015 5
GTIN	4067263733119
Item class	01L

Description

Version:

GARANT Green Plus **ultrasonic cleaner** – top performance with maximum flexibility. Do you work with complex workpiece geometries and delicate surfaces? Then the Sonic Cleaner series is made for you. The cleaning series from GARANT GreenPlus, specially designed for ultrasonic systems, includes alkaline, acid and neutral cleaners for a wide variety of materials and fields of application. Depending on the requirements and degree of dirt, the highly concentrated cleaners can be diluted and are powerful even at room temperature. This makes optimum use of the medium. Their long service life also saves time and money. All Sonic Cleaners are **hazard-label-free, biologically degradable, VOC-free and silicate-free**. For companies, this means the products are easy to handle and ensures both your employees and the environment are protected.

Sonic Cleaner AL-D, **alkaline demulsifying** cleaning concentrate for general-purpose ultrasonic applications and an extremely long service life with high material compatibility.

Application:

For ultrasonic cleaning baths.

Emulsions, oils, greases, drawing greases, anti-corrosion agents, grinding dust, soot, inks, toners, lapping and polishing agents.

Suitable for:

Common materials such as steel and non-ferrous metals, glass, plastic, ceramic, rubber. High material compatibility – check in advance in the case of sensitive surfaces.

Technical description

Storage temperature	20 - 80 °C
Fill capacity liquid	5 l
Mixing ratio	3 – 10 %
pH value	10
Sustainability	GARANT GreenPlus
Series	GreenPlus
Product name attribute	alkaline demulsifying
Type of product	Ultrasonic power cleaner