



LED cordless lamp 0 version without battery, 18 V, Type: M18HOAL



Order data

Order number	073211 M18HOAL
GTIN	4058546340513
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity.

- **LED floodlight with TrueView™ technology and 120° rotating radiator head.**
- **Hybrid power source: operates either with an 18V rechargeable battery or with a cable.**

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Power supply	Mains operated
Number of rechargeable batteries contained	0
Bulb	LED module
Battery voltage	18 V
Illumination step 2	2000 lm

Illumination	4000 lm
Manufacturer's designation	M18 HOAL
Type of rechargeable battery	Lithium-ion
Illumination step 3	1200 lm
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp