

HEDI

All-plastic cable drum, Type: 50R



Order data

Order number	081103 50R
GTIN	4003644024186
Item class	08B

Description

Version:

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Compact, high-quality HEDI® all-plastic cable reels with a reel diameter of 250 mm and ergonomic and safety features.

- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Easy to mount on a wall.**

Approved for short-term use in the open air.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Diagnostic system present	yes
---------------------------	-----

Material of body	Plastic
Cable class	H05RR-F
Rated power unrolled	3500 (16 A) W
Cable structure	3G1.5
Power supply	Mains-powered
Cable length	50 m
Cable colour	black
IP Index of Protection	IP 44
Number of sockets	3
Nominal voltage	250 V
Material cable	Rubber
Type of product	Cable drum