

# HEDI

## All-plastic cable drum, Type: 25V



### Order data

Order number	081118 25V
GTIN	4003644024810
Item class	08B

### Description

#### Version:

HEDI® cable reels stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches. Affordable HEDI® all-plastic cable reel with a reel diameter of 250 mm.

- **Inclined 3 degrees for greater ground clearance and to make it comfortable to carry.**
- **Easy to mount on a wall.**

#### Function:

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

### Technical description

Diagnostic system present	no
Power supply	Mains-powered
IP Index of Protection	IP 20
Material of body	Plastic

Cable colour	red
Nominal voltage	250 V
Cable structure	3G1.5
Rated power unrolled	3500 (16 A) W
Material cable	PVC
Cable length	25 m
Number of sockets	4
Cable class	H05VV-F
Type of product	Cable drum