

HEDI

All-plastic cable drum for F, B, PL and CZ, Type: 25V



Order data

Order number	081119 25V
GTIN	4003644024827
Item class	08B

Description

Version:

HEDI® cable reels stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches. Affordable HEDI® all-plastic cable reel with a reel diameter of 250 mm.

- **Inclined 3 degrees for greater ground clearance and to make it comfortable to carry.**
- **Easy to mount on a wall.**

With sockets for **France, Belgium, Poland and the Czech Republic.**

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Technical description

Nominal voltage	250 V
Cable colour	red
IP Index of Protection	IP 20

Rated power unrolled	3500 (16 A) W
Cable structure	3G1.5
Number of sockets	4
Material of body	Plastic
Material cable	PVC
Cable length	25 m
Diagnostic system present	no
Power supply	Mains-powered
Cable class	H05VV-F
Type of product	Cable drum