

Garant

Shoe, black comfort black safety shoe ESD, S1 W1, EU shoe size: 39



Order data

Order number	092159 39
GTIN	4067263778998
Item class	01S

Description

Version:

GARANT comfort safety shoes combine the highest possible wearing comfort with modern design. Innovative and high-quality materials coupled with very high-quality workmanship "Made in Germany" guarantee very high protection combined with minimum weight. Different calf widths (width W1 for normal width feet, width W2 for wider feet) and the tweaked manufacturing technique permits a "true" multi-width system and thus create an ideal solution to the requirement for different widths of feet. The rigorous implementation of ergonomic principles and exchangeable weight-dependent damping significantly reduce the stresses on the knee and back, and thus contribute appreciably to long-term health.

- **The material of the uppers is light-weight but hard-wearing micro-fibre.**
- **Breathable functional lining.**
- **Practical GARANT comfort heel-puller allows the shoes to be put on quickly and easily.**
- **GARANT comfort insoles with weight-dependent damping.**
- **Outer sole GARANT comfort TPU.**
- **Protection against electrostatic discharge (ESD).**

Shoe with large area ventilation structure.

Standard:

EN ISO 20345:2011 S1 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

- **For GARANT comfort insoles with weight dependent shock absorption, see accessories for foot protection under: 092864 (soft), 092865 (medium), 092866 (hard).**

- **Shoes of sizes 36-39 are supplied as standard with soft damping, sizes 40-45 with medium damping and sizes 46-48 with hard damping.**
- **See accessories for foot protection for the appropriate GARANT shoelaces under: 092855 120.**

Wide fitting W2, see No. 092160.

electrostatic characteristic: EGB/ESD

Protection class: S1

Material of protective toe-cap: Aluminium

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Vario® damping

Technical description

Material of protective toe-cap	Aluminium
Standard	Inlay type-tested according to DGUV regulation 191
Protection class	S1
EU shoe size	39
Characteristics	Vario® damping
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes