

HEDI

All-plastic cable drum, Type: 50V



Order data

Order number	081118 50V
GTIN	4003644024834
Item class	08B

Description

Version:

HEDI® cable reels stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches. Affordable HEDI® all-plastic cable reel with a reel diameter of 250 mm.

- **Inclined 3 degrees for greater ground clearance and to make it comfortable to carry.**
- **Easy to mount on a wall.**

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Technical description

Cable colour	red
Cable class	H05VV-F
Number of sockets	4
Cable structure	3G1.5

Power supply	Mains-powered
Material of body	Plastic
IP Index of Protection	IP 20
Rated power unrolled	3500 (16 A) W
Diagnostic system present	no
Cable length	50 m
Material cable	PVC
Nominal voltage	250 V
Type of product	Cable drum