



Earplugs, electronic Impact in-EAR PRO, Type: IE_PRO



Order data

Order number	097783 IE_PRO
GTIN	3603830341076
Item class	09A

Description

Version:

The Impact In-Ear PRO is an electronic earplug with volume and gain control. These reproduce sound realistically and authentically thanks to the **hear-through function** with separate control. The gain is limited to a safe maximum level and stops when the ambient volume exceeds 82 db. In addition, the Impact In-Ear PRO can be connected to, for example, a phone via **Bluetooth**.

- **Hear-through volume can be adjusted separately in 6 levels.**
- **Bluetooth volume can be adjusted separately in 15 levels.**

The 200 mAh battery can be fully recharged within 2 hours via the USB-C port. The Impact In-Ear PRO has flexible and malleable ear hooks for comfortable wearing. The reusable silicone pods are available in three different sizes, depending on the ear canal.

SNR = 30 dB (H = 28 dB, M = 29 dB, L = 29 dB)

Application:

For communication in demanding environments with high and varying noise levels.

Standard:

EN 352-2; EN 352-7; EN 352-9; EN 352-10

Supplied with:

1x Impact in-Ear PRO, 1x transport box, 1x USB /type-C charging cable, 1x user manual, 2x replacement PODS SMALL, 2x replacement PODS MEDIUM, 2x replacement PODS LARGE.

Technical description

SNR value (noise attenuation)	30 dB(A)
Series	Impact in-EAR PRO
Working time	10 h
Power supply	Mains operated
Standard	EN 352-7
Standard	EN 352-2
Type of product	Ear defenders