

Garant
**Side lock arbor Form AD with cooling channel bore, BT 30 A = 100, Clamping
 Ø D1: 16mm**

Order data

Order number	302591 16
GTIN	4067263983958
Item class	31A

Description
Version:

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	16
External Ø D	48 mm
Overhang dimension A	100 mm
Clamping Ø D ₁	16 mm
Adapter	BT 30 A = 100
Standard	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	AD

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor