

**Garant**
**Side lock arbor Form AD with cooling channel bore, BT 30 A = 100, Clamping Ø D1: 10mm**

**Order data**

Order number	302591 10
GTIN	4067263983934
Item class	31A

**Description**
**Version:**

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping Ø D <sub>1</sub>	10 mm
External Ø D	35 mm
Spare clamping screw No. 30 9900	10
Overhang dimension A	100 mm
Adapter	BT 30 A = 100
Standard	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	AD

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor