



## Safety cable reel, Type: 10S



### Order data

Order number	081192 10S
GTIN	7391390467041
Item class	08A

### Description

#### Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling, with **180° pivoting range**.

#### Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

#### Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

#### Note:

For spring return hose reels see No. 080066 to 080079.

### Technical description

Power supply	Mains-powered
Material cable	Neoprene rubber
Height	313 mm

Nominal voltage	240 V
Cable structure	3G2.5
Rated power unrolled	3500 W
Body material	Plastic
Cable length	10 m
Width	190 mm
Cable class	H07RN-F
IP Index of Protection	IP 44
Length	406 mm
Type of product	Cable reel