

Garant
**Side lock arbor Form AD with cooling channel bore, BT 30 A = 100, Clamping
Ø D1: 20mm**

Order data

Order number	302591 20
GTIN	4067263983965
Item class	31A

Description
Version:

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	100 mm
Clamping Ø D ₁	20 mm
Spare clamping screw No. 30 9900	20
Adapter	BT 30 A = 100
Standard	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor