

Garant
Side lock arbor, HSK-A 63 A = 100, Clamping \varnothing D1: 6mm

Order data

Order number	304309 6
GTIN	4067263014478
Item class	31A

Description
Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth running!).

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890.

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Overhang dimension A	100 mm
Clamping \varnothing D ₁	6 mm
Spare clamping screw No. 30 9900	6
External \varnothing D	25 mm
Adapter	HSK-A 63 A = 100
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1

Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 6 mm	309900 6
---	----------