



Spur-gear block and tackle Tralift™, Safe working load: 0,25t



Order data

Order number	086019 0,25
GTIN	2050001747013
Item class	08Y

Description

Version:

Each spur-gear block and tackle is factory overload-tested and supplied with a user manual and test certificate.

All-steel construction. Needle bearings and ball bearings on all rotating parts. Automatic load pressure brake. 360° rotating forged hook.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Note:

Lifting capacity up to 20 tons, chain box and overload protection available on request.

Lifting force at nominal load: 11 daN

Standard lifting height: 3 m

Number of chains: 1

Safe working load: 250 kg

Weight: 3.2 kg

Technical description

Standard lifting height	3 m
-------------------------	-----

Lifting force at nominal load	11 daN
Housing material	All-steel
Safe working load in t	0.25 t
Number of chains	1
Safe working load	250 kg
Weight	3.2 kg
Type of product	Bottle jack