


**Toolholder, form B1 radial right-hand, short, Shank  $\varnothing$  d1: 16mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 319007 16     |
| GTIN         | 4067263014263 |
| Item class   | 32V           |

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

|                            |        |
|----------------------------|--------|
| Colour code for VDI shanks | VDI 16 |
| $l_2$                      | 24 mm  |
| $l_1$                      | 13 mm  |
| $h_1$                      | 12 mm  |
| $h_5$                      | 20 mm  |
| $b_1$                      | 42 mm  |
| $b_2$                      | 23 mm  |

|                        |                |
|------------------------|----------------|
| h <sub>2</sub>         | 17 mm          |
| Shank Ø D <sub>1</sub> | 16 mm          |
| h <sub>6</sub>         | 30 mm          |
| Shape                  | B              |
| Type of product        | VDI tool arbor |