


**Toolholder, form B1 radial right-hand, short, Shank  $\varnothing$  d1: 20mm**

**Order data**

Order number	319007 20
GTIN	4067263014270
Item class	32V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

b <sub>2</sub>	30 mm
b <sub>1</sub>	55 mm
Colour code for VDI shanks	VDI 20
Shank $\varnothing$ D <sub>1</sub>	20 mm
h <sub>1</sub>	16 mm
h <sub>5</sub>	25 mm
l <sub>1</sub>	16 mm

$l_2$	30 mm
$h_2$	22 mm
$h_6$	30 mm
Shape	B
Type of product	VDI tool arbor