

**Toolholder form B2 radial left-hand, short, Shank \varnothing d1: 50mm****Order data**

Order number	319017 50
GTIN	4067263201151
Item class	32V

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_1	32 mm
h_2	41 mm
Shank \varnothing D ₁	50 mm
Colour code for VDI shanks	VDI 50
l_2	55 mm
b_1	100 mm

b_2	50 mm
h_5	36 mm
l_1	30 mm
Shape	B
Type of product	VDI tool arbor