

**Toolholder form B2 radial left-hand, short, Shank  $\varnothing$  d1: 40mm****Order data**

Order number	319017 40
GTIN	4067263201144
Item class	32V

**Description****Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$b_2$	42.5 mm
$b_1$	85 mm
$h_5$	32.5 mm
$h_1$	25 mm
$h_2$	25 mm
Shank $\varnothing$ D <sub>1</sub>	40 mm

$l_1$	22 mm
Colour code for VDI shanks	VDI 40
$l_2$	44 mm
Shape	B
Type of product	VDI tool arbor