


Toolholder form B4 radial left-hand, short, Shank \varnothing d1: 40mm

Order data

Order number	319037 40
GTIN	4067263201243
Item class	32V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

l_2	44 mm
b_1	85 mm
Colour code for VDI shanks	VDI 40
b_2	42.5 mm
h_5	32.5 mm

h ₁	25 mm
Shank Ø D ₁	40 mm
l ₁	22 mm
h ₆	48 mm
h ₂	25 mm
Shape	B
Type of product	VDI tool arbor