

**Toolholder form B4 radial left-hand, short, Shank  $\varnothing$  d1: 50mm****Order data**

Order number	319037 50
GTIN	4067263201250
Item class	32V

**Description****Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$h_2$	41 mm
Colour code for VDI shanks	VDI 50
$h_6$	60 mm
$h_1$	32 mm
$b_1$	100 mm

Shank $\varnothing D_1$	50 mm
$h_5$	50 mm
$l_1$	30 mm
$b_2$	50 mm
$l_2$	55 mm
Shape	B
Type of product	VDI tool arbor