



## Toolholder form B3 radial right-hand, short, Shank $\varnothing$ d1: 16mm



### Order data

Order number	319027 16
GTIN	4067263201168
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

Mainly for external machining.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

$l_2$	24 mm
$h_5$	20 mm
$b_1$	42 mm
$h_6$	30 mm
$h_1$	12 mm
Shank $\varnothing$ D <sub>1</sub>	16 mm
$h_2$	17 mm

$l_1$	13 mm
Colour code for VDI shanks	VDI 16
$b_2$	23 mm
Shape	B
Type of product	VDI tool arbor