



Toolholder form B3 radial right-hand, short, Shank \varnothing d1: 50mm



Order data

Order number	319027 50
GTIN	4067263201205
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	50 mm
h ₆	60 mm
l ₁	30 mm
l ₂	55 mm
h ₅	50 mm
h ₂	41 mm
Colour code for VDI shanks	VDI 50

h_1	32 mm
b_1	100 mm
Shank $\varnothing D_1$	50 mm
Shape	B
Type of product	VDI tool arbor