

**Toolholder form B4 radial left-hand, short, Shank \varnothing d1: 30mm****Order data**

Order number	319037 30
GTIN	4067263201236
Item class	32V

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank \varnothing D ₁	30 mm
l ₁	22 mm
h ₆	38 mm
h ₅	28 mm
b ₂	35 mm

l_2	40 mm
h_1	20 mm
Colour code for VDI shanks	VDI 30
b_1	70 mm
h_2	29 mm
Shape	B
Type of product	VDI tool arbor