



## Toolholder form B5 radial right-hand, long, Shank $\varnothing$ d1: 30mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 319047 30     |
| GTIN         | 4067263201281 |
| Item class   | 32V           |

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

Mainly for external machining.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

|                                    |        |
|------------------------------------|--------|
| Colour code for VDI shanks         | VDI 30 |
| Shank $\varnothing$ D <sub>1</sub> | 30 mm  |
| l <sub>2</sub>                     | 40 mm  |
| b <sub>2</sub>                     | 65 mm  |
| h <sub>2</sub>                     | 29 mm  |
| l <sub>1</sub>                     | 22 mm  |
| h <sub>1</sub>                     | 20 mm  |

|                 |                |
|-----------------|----------------|
| b <sub>1</sub>  | 100 mm         |
| h <sub>5</sub>  | 28 mm          |
| Shape           | B              |
| Type of product | VDI tool arbor |