



Toolholder form B6 radial left-hand, long, Shank \varnothing d1: 30mm



Order data

Order number	319057 30
GTIN	4067263201335
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Colour code for VDI shanks	VDI 30
h_1	20 mm
b_1	100 mm
l_1	22 mm
Shank \varnothing D ₁	30 mm
h_5	28 mm

h_2	29 mm
b_2	65 mm
l_2	40 mm
Shape	B
Type of product	VDI tool arbor