



Toolholder form B6 radial left-hand, long, Shank \varnothing d1: 40mm



Order data

Order number	319057 40
GTIN	4067263201342
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

l_2	44 mm
b_1	118 mm
Shank \varnothing D ₁	40 mm
b_2	75.5 mm
h_2	25 mm
l_1	22 mm

h ₁	25 mm
h ₅	32.5 mm
Colour code for VDI shanks	VDI 40
Shape	B
Type of product	VDI tool arbor