



Clamping hook, cylindrical, Type: 1



Order data

Order number	370076 1
GTIN	4059245030828
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished. Screw head resting on clamping hook when mounting.

Application:

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

Optional extras:

Springs and socket-head screws on request

Technical description

Height H_2	10 mm
$F_{max.}$	4.8 kN
H_1	42 mm
$\varnothing D$	16 mm

Data sheet

$\varnothing D_3$	6.5 mm
B	11 mm
$\varnothing D_2$	11 mm
$\varnothing D_1$	10 mm
Type of product	Clamping hook