

**Clamping hook, cylindrical, Type: 3****Order data**

|              |               |
|--------------|---------------|
| Order number | 370076 3      |
| GTIN         | 4059245030842 |
| Item class   | 37K           |

**Description**

## Version:

Entirely of hardened and tempered steel; burnished. Screw head resting on clamping hook when mounting.

## Application:

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

## Optional extras:

Springs and socket-head screws on request

**Technical description**

|                   |         |
|-------------------|---------|
| Height $H_2$      | 16 mm   |
| $H_1$             | 66 mm   |
| $F_{max.}$        | 13.9 kN |
| $\varnothing D_2$ | 18 mm   |

## Data sheet

|                  |               |
|------------------|---------------|
| B                | 17 mm         |
| Ø D <sub>3</sub> | 10.5 mm       |
| Ø D <sub>1</sub> | 14 mm         |
| Ø D              | 25 mm         |
| Type of product  | Clamping hook |