



## Clamping hook, cylindrical, Type: 2



### Order data

Order number	370075 2
GTIN	4059245030804
Item class	37K

### Description

**Version:**

Entirely of hardened and tempered steel; burnished. With countersunk screw. Screw head recessed in the clamping hook.

**Application:**

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

**Optional extras:**

Springs and socket-head screws on request

### Technical description

$F_{max.}$	8.8 kN
Height $H_2$	12 mm
$H_1$	52 mm
$\varnothing D_2$	15 mm

## Data sheet

Ø D	20 mm
Ø D <sub>1</sub>	12 mm
Ø D <sub>3</sub>	8.5 mm
B	15 mm
Type of product	Clamping hook